

## ExStik<sup>®</sup> Flat Surface Electrodes



**Rugged, flat surface electrode provides “On-the-Spot” measurements with an ExStik<sup>®</sup> meter**

*Ideal for direct contact applications such as food, paper, cement and wet surface*

### Features:

- Flat surface electrode allows “On-the-Spot” measurements whether the sample is liquid, semi-solid or solid
- Chlorine and pH electrodes have built-in temperature sensor
- Chlorine electrode does not require a reference solution and also does not have a shelf life
- Flat surface design provides a rigid structure that is difficult to damage, but easy to clean

**ExStik<sup>®</sup> pH, Chlorine, and ORP Electrodes are to be used with ExStik<sup>®</sup> meters only**



### Ordering Information:

- PH105 .....pH ExStik<sup>®</sup> Electrode Module  
 CL205 .....Chlorine ExStik<sup>®</sup> Electrode Module  
 RE305 .....ORP ExStik<sup>®</sup> Electrode Module  
 PH115 .....Refillable pH ExStik<sup>®</sup> Electrode Module  
 PH113 .....Reference Refilling Solution Kit for PH115  
 CL200 .....ExStik<sup>™</sup> Chlorine Meter  
 RE300 .....ExStik<sup>™</sup> ORP Meter  
 CL203 .....Reagent tablets (10pk - 100 tests)  
 EX006 .....Weighted base with 5 solution cups  
 EX007 .....Spare sample solution cups (24pk)  
 PH103 .....Tripak buffers (6ea. of 4, 7, 10pH & 2 Rinsing solutions)

สนใจติดต่อ บริษัท เอเมท จำกัด 31 ซอย โกศลรวมใจ 37 แยก 2 แขวงดอนเมือง เขต ดอนเมือง กรุงเทพฯ. 10210

โทร.02-503-8900, แฟกซ์ : 02-981-0181, 02-981-0182 email : [sales@amet.net](mailto:sales@amet.net) , Web: [www.amet.net](http://www.amet.net)